




HEX/Allen screw

Screw thread

Cable diameter without rubber bushing:
ØF min: 3 mm
ØF max: 8.5 mm

Cable diameter with rubber bushing:
ØF max: 8 mm

Cable diameter without reduction plate:
ØF max: 12.5 mm

09670250320	4-40 UNC-2A
Part number	Screw thread

 		All Dimensions in mm Original Size DIN A4		Scale 1:1	Free size tol.		Ref.	
							Sub.	
	All rights reserved			Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-02-14	State Final Release
	Department EC PD - FR							
HARTING Electronics GmbH D-32339 Espelkamp				Title D-Sub 25-poles metal hood top entry				Doc-Key / ECM-Nr. 100567867/UGD/001/A 500000071307
				Type TB	Number 09670250320			Rev. A