

Representative Image

Catalog No. RA867

Description: INS VINYL RNG TRM 22-16 BLT No8 RED

UPC No 786210817453

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Vinyl-Insulated Ring Terminal, Length .97 Inches, Width .31 Inches, Maximum Insulation .150, Bolt Hole #8, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated, 1,000 Pack

Descriptors

Category	Electrical terminals
Special Features	These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wires flex point. Brazed seam barrel is serrated to obtain high pull-out value.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Red

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	22-16 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	Polyvinyl chloride (PVC)
Colour insulation	Red
Reel packaging	N
AWG-range	22-18

by ABB

Downloaded from Arrow.com.

ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	8

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.