



Pushing Performance
Since 1945

Plug socket module Swiss



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0012
Specification	Plug socket module Swiss
HARTING eCatalogue	https://harting.com/39500010012

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket

Version

Termination method	Spring clamp termination
Field of application	Switzerland

Termination data

Supply voltage	250 V AC
Nominal current	10 A
Nominal frequency	50 Hz

Technical characteristics

Conductor cross-section	1.5 mm²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	65 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140190450
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406