




NOTES:  
 1. ALL PARTS TO BE BULK PACKED.  
 2. CONTACTS ASSEMBLED INTO CONNECTOR.  
 3. ALL DIMENSIONS ARE REFERENCE ONLY  
 EXCEPT WHERE NOTED WITH A TOLERANCE.  
 DIMENSIONS IN BRACKETS [ ] ARE METRIC.  
 4. PC TAIL LENGTH OPTIONS:  
 • STANDARD (SHORT) TAIL = 0.107in [W4281-1XSG-3ES]  
 • INTERMEDIATE = 0.202in [W4291-1XSG-3ES]  
 • LONG = 0.267in [W4292-1XSG-3ES]





**MATING VIEW**  
W4291-10SG-300  
10-POS.




**MATING VIEW**  
W4291-11SG-300  
11-POS.

**MATING VIEW**  
W4291-12SG-300  
12-POS.



**PC TAIL LAYOUT**

**RECOMMENDED  
PANEL CUTOUT**  
STANDARD MULTI-CON-X



**PC TAIL VIEW**  
W4291-10SG-300 - 10-POS. (11&12 CLOSED)  
W4291-11SG-300 - 11-POS. (12 CLOSED)  
W4291-12SG-300 - 12-POS. (ALL OPEN)

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4291-10SG-300	10 - #20	11, 12
W4291-11SG-300	11 - #20	12
W4291-12SG-300	12 - #20	NONE
W4291-1XSG-300		

NO. OF CONTACTS

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1
REV.	INIT.	DATE	DESCRIPTION
ORIG. DRAWN BY: DATE: PAK 10/22/14			CHECKED BY:
APPROVED BY:			TITLE: PANEL SOCKET, E-KEY
SCALE NTS	SIZE B	SHEET 1 OF 1	12-POS., #20 PC TAIL, INTERMEDIATE
> CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			MULTI-CON-X, WEATHER RESISTANT
FILE: W4291-1XSG-300			CUSTOMER: STANDARD PRODUCT
DIRECTORY: SLW			PART NUMBER: W4291-1XSG-300
			REV A

**CUSTOMER APPROVAL**

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_