



Part Number : [5056080000](#)
Product Description : 2.50mm and 3.30mm
Pitch Crimp Terminal, Male, 22-18 AWG, Reel
Series Number : 505608
Status : Active
Product Category : Crimp Terminals
Packaging Alternative : 5056080100 (Bag)



Documents & Resources

Drawings

[5056080000_sd.pdf](#)

3D Models and Design Files

[5056080000_stp.zip](#)

Specifications

- [5056050000-A01.pdf](#)
- [AS-504693-001-001.pdf](#)
- [AS-504693-002-001.pdf](#)
- [5056050000-A00.pdf](#)
- [5056089200-200.pdf](#)
- [PS-504693-001-001.pdf](#)
- [5056050000-000.pdf](#)

Tooling Specifications

[5056070000-C00.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	505608
Description	2.50mm and 3.30mm Pitch Crimp Terminal, Male, 22-18 AWG, Reel
Application	Signal, Wire-to-Wire
Product Name	CP-3.3
UPC	889056802413

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	300V AC (RMS)/DC

Physical

Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	102.000/mg
Packaging Type	Reel
Plating min - Mating	0.914µm

Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.55-2.60mm
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
CP-3.3 Single Row Plug Housings	<u>504694</u>
CP-3.3 Dual Row Plug Housings	<u>505606</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for CP-3.3 Wire-to-Wire Plug and Receptacle Terminals, 22-18 AWG, UL1007 Wire	<u>2002184000</u>
FineAdjust Applicator for CP 3.3 Wire-to-Wire Plug and Receptacle Terminals, 22-18 AWG	<u>2037022300</u>
Extraction Tool for MTC (Multi Terminal Connector) Female Terminal, 18-14 AWG	<u>638138600</u>
FineAdjust Applicator for CP 3.3 Wire-to-Wire Plug and Receptacle Terminals, 22-20 AWG	<u>2037023300</u>

Application Tooling

Japan

Description	Part Number
S-1 Applicator for CP-3.3 Terminals, 22-18 AWG	<u>2014003700</u>

This document was generated on Apr 26, 2025