



Part Number : [936030087](#)
Product Description : Heavy-Duty Connector Kit, 24 Pole, Series S-E Female-Male Inserts, Pg21 Die-cast Aluminum Hood-Top Entry, Surface Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey
Series Number : 93603
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7924.6767.0



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93603
Description	Heavy-Duty Connector Kit, 24 Pole, Series S-E Female-Male Inserts, Pg21 Die-cast Aluminum Hood-Top Entry, Surface Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Kit Component Parts	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 16B «77x27», Extended Pg21 Thread, Grey, Heavy-Duty Screw Terminal Insert, Male, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27», Heavy-Duty Screw Terminal Insert, Female, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27», Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», Pg21 Thread, Grey
Product Name	Heavy-Duty Connectors
UPC	887191865096

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Component Size	24B «104X27»
Lock to Mating Part	Yes
Mounting Style	Surface Mount
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

Kit Component Parts

Description	Part Number
Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 16B «77x27», Extended Pg21 Thread, Grey	<u>936012781</u>
Heavy-Duty Screw Terminal Insert, Male, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»	<u>936010307</u>
Heavy-Duty Screw Terminal Insert, Female, 24-Pole, 16A, Numbered 1-24, with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»	<u>936010297</u>
Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», Pg21 Thread, Grey	<u>936013500</u>

This document was generated on Sep 17, 2025