

## Protect It! 2-Outlet Portable Surge Protector, Direct Plug-In, 1050 Joules, Fax/Modem Protection

MODEL NUMBER: **TRAVELER**



### Highlights

- 2 outlets/Direct plug-in
- 1050 joule rating
- Retractable plug
- Modem/fax surge protection

### Package Includes

- TRAVELER Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

### Description

Tripp Lite's portable TRAVELER surge suppressor offers complete AC and phone line surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact portable housing weighing less than 4 ounces neatly fits into laptop travel cases. Retractable plug prevents scratching of expensive portable electronics. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines. TRAVELER offers 2 total outlets in a space saving direct plug-in format and diagnostic LEDs to warn of wiring problems and suppressor damage. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 2 NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Direct plug-in suppressor hangs off of standard wall socket

SUPPRESSION: AC: 140V RMS Clamping/1050 joules/330V UL1449 Let-through Rating

PHONE: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

### Features

- 1050 joules AC surge suppression shields equipment from the strongest surges and line noise
- 2 AC outlets with room for 2 transformer plugs without blocking outlets covers computer and one peripheral
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Extra-small portable housing weighing less than 4 ounces neatly fits into laptop travel cases - retractable input plug prevents scratching of laptops and other devices



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

| OVERVIEW                           |                                                                                                      |
|------------------------------------|------------------------------------------------------------------------------------------------------|
| UPC Code                           | 037332116185                                                                                         |
| INPUT                              |                                                                                                      |
| Nominal Input Voltage(s) Supported | 120V AC                                                                                              |
| Recommended Electrical Service     | 120V (110-125V)                                                                                      |
| Input Cord Length Details          | Direct plug-in                                                                                       |
| Voltage Compatibility (VAC)        | 120                                                                                                  |
| Maximum Surge Amps                 | 30000                                                                                                |
| Input Plug Type                    | NEMA 5-15P                                                                                           |
| Input Cord Length (ft.)            | 0                                                                                                    |
| Right-Angle Plug                   | No                                                                                                   |
| Input Cord Length (m)              | 0.00                                                                                                 |
| Integrated Cord Clip               | No                                                                                                   |
| OUTPUT                             |                                                                                                      |
| Frequency Compatibility            | 50 / 60 Hz                                                                                           |
| Output (Watts)                     | 1800                                                                                                 |
| Output Receptacles                 | (2) 5-15R                                                                                            |
| Circuit Breaker (amps)             | 15                                                                                                   |
| Transformer Accommodation          | (2) Yes                                                                                              |
| Right-Angle Outlets                | No                                                                                                   |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                                                      |
| Diagnostic LED(s)                  | Yes                                                                                                  |
| Diagnostic LED Details             | Two built-in LEDs confirm suppressor "protection present" (green) and outlet "grounded" (red) status |
| SURGE / NOISE SUPPRESSION          |                                                                                                      |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

|                                     |                                                                                    |
|-------------------------------------|------------------------------------------------------------------------------------|
| AC Suppression Joule Rating         | 1050                                                                               |
| AC Suppression Response Time        | < 1 ns                                                                             |
| Protection Modes                    | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS)              | 150                                                                                |
| UL1449 Let Through Rating           | 400V - UL Verified                                                                 |
| Automatic Shut-Off                  | No                                                                                 |
| <b>DATALINE SURGE SUPPRESSION</b>   |                                                                                    |
| Telephone/DSL Protection            | Yes                                                                                |
| Telephone/DSL Protection Details    | 1 line                                                                             |
| Cable (Coax) Protection             | No                                                                                 |
| Network (Ethernet) Protection       | No                                                                                 |
| <b>PHYSICAL</b>                     |                                                                                    |
| Color                               | Black                                                                              |
| Antimicrobial Coating               | No                                                                                 |
| Form Factors Supported              | Direct plug-in connection enables mounting to any AC wall receptacle               |
| Integrated Keyhole Mounting Slots   | No                                                                                 |
| Material of Construction            | Plastic                                                                            |
| Receptacle Color                    | Black                                                                              |
| Shipping Dimensions (hwd / cm)      | 10.16 x 10.16 x 5.08                                                               |
| Shipping Dimensions (hwd / in.)     | 4.00 x 4.00 x 2.00                                                                 |
| Shipping Weight (kg)                | 0.19                                                                               |
| Shipping Weight (lbs.)              | 0.42                                                                               |
| Unit Dimensions (hwd / cm)          | 8.9 x 6.4 x 4.4                                                                    |
| Unit Dimensions (hwd / in.)         | 3.5 x 2.5 x 1.75                                                                   |
| Unit Weight (kg)                    | 0.14                                                                               |
| Unit Weight (lbs.)                  | 0.3                                                                                |
| <b>SPECIAL FEATURES</b>             |                                                                                    |
| Rotatable Outlets                   | No                                                                                 |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                                                                    |
| Canada                              | cUL                                                                                |
| Approvals                           | Exceeds IEEE 587 category A&B specifications                                       |
| UL1449 3rd Edition (AC Suppression) | UL1449                                                                             |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                                            |                                                                                                                       |
|------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| NOM (Mexico)                                               | NOM                                                                                                                   |
| UL1363 (Power Tap)                                         | UL1363                                                                                                                |
| UL497A (Communications)                                    | UL497A                                                                                                                |
| FCC Part 68 (Communications)                               | FCC Part 68                                                                                                           |
| Industry Canada (Communications)                           | Industry Canada                                                                                                       |
| <b>WARRANTY</b>                                            |                                                                                                                       |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                                                                                             |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>