

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430224

Status:

Active

Overview:

Watertite® Wet-Location Wiring Solutions

Description:

Watertite® Cordset 12 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L5-20 125V, Inline GFCI

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
IP Rating	IP67
NEMA Configuration	NEMA L5-20
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678871267
Woodhead	Yes
Physical	
Cord Grip Body Size	F3 3/4"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Locking Blade	Yes
Poles	2-pole/3-wire
Electrical	
Cord Type	12/3 SJOW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Lighted Connector	No
Voltage - Maximum	125V
Material Info	
Old Part Number	26W47B123IN



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION