


Series
NSX

SIZE 12 REAR RELEASE, REAR REMOVABLE CRIMP SOCKET CONTACT
REDUCED BARREL FOR AWG 18 - 20 - 22 -24

Issue:
Apr. 27, 16

Page
1/1



MATERIALS :

CONTACT BODY : BERYLLIUM COPPER PER ASTM B 196

PROTECTIVE SLEEVE : STAINLESS STEEL PER SAE AMS-5514

FINISH :

CONTACT BODY : PLATING .00005 INCH OF GOLD PER MIL-DTL-45204 OVER NICKEL PER SAE AMS 2403
CONTACT PROTECTIVE SLEEVE : PASSIVATED


WIRES ACCOMODATED : AWG 18 - 20 - 22 -24

INSULATION DIAMETER : 3,43 (.135) MAX
STRIP LENGTH : 6 (.236)


TOOLING :

CRIMPING TOOL : M22520/1-01 RADIALl 282291
SELECTOR POSITION : 5 FOR AWG 18
4 FOR AWG 20
3 FOR AWG 22
2 FOR AWG 24

POSITIONER : M22520/1-02 RADIALl 282972
INSERTION AND EXTRACTION TOOL : M81969/28-02 RADIALl 282945



DIMENSIONS : mm (inch are given for information only)



Estimated weight : 1.35 g

CREATION

PEN: /

NOM: Macari JP.

DATE: Jan. 24, 1989

APPR.: /

Apr. 27, 16	Updated 3D view	Pecault B.	Legendre T.	
Aug. 04, 14	Updated	Branjonneau	Moutault	
Issue	Revisions	Name	Approved	

620341EN

RADIALl PROPRIETARY INFORMATION

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from RADIALl. This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary.

4112_9311