

PART NAME	STEEL INTERNAL PANEL	PART No.	NBX-10980 to NBX-10990	NBX-10983 to NBX-10994	NBX-10985 to NBX-10996	NBX-10987 to NBX-10997	REV. DATE	10-18-11
MATERIAL: 16 GA. STEEL FINISH: GALVANIZED 0.315 DIA. (4) HOLES 0.344 RADIUS (4) PLACES TOLERANCE = ±0.039 [±1] DIMENSIONS = INCHES [MILLIMETERS] A B D C ALL PANELS ARE SUPPLIED WITH QTY. (4) M5 x 10mm LG. TRUSS HD. PHILLIPS DRIVE STAINLESS STEEL MACHINE SCREWS								
PART NO.	A	B	C	D				
NBX-10980	6.735 [171]	5.043 [128]	10.550 [268]	8.858 [225]				
NBX-10981	10.443 [265]	8.937 [228]	14.252 [362]	12.795 [325]				
NBX-10982	14.282 [363]	12.913 [328]	18.228 [463]	16.850 [428]				
NBX-10983	13.897 [353]	12.874 [327]	21.771 [553]	20.669 [525]				
NBX-10985	6.378 [161]	4.726 [120]	9.922 [252]	8.238 [209.25]				
NBX-10986	11.457 [291]	9.847 [250]	11.457 [291]	9.847 [250]				
NBX-10987	10.433 [265]	8.937 [227]	14.252 [362]	12.795 [325]				
NBX-10990	13.120 [333]	11.620 [295]	17.620 [447]	16.120 [409]				
NBX-10994	6.378 [161]	4.726 [120]	13.937 [354]	12.205 [310]				
NBX-10996	10.000 [254]	8.228 [209]	12.362 [314]	10.590 [269]				
NBX-10997	10.000 [254]	8.228 [209]	13.858 [352]	12.166 [309]				