



Board Layout 3:1



3) recommended drill hole dia.: $\varnothing 0,64 \pm 0,01$
through hole dia. (after plating): $\varnothing 0,55 \pm 0,05$
(acc. to IEC 60352-5)

2) non-metallized drillings
1) fixing-hole optional

X 5:1



 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maßel Free size tolerances	
				Dat.	Name	Maßstab/Scale 2:1 (3:1,5:1)	AdvancedMC for ATCA type B+ connector 170 pole, press-fit	
			Detail.	09.11.06	Hl.			
			Insp.	09.11.06	Hm			
			Stand.					
34010			HARTING Electronics GmbH & Co. KG				TB 16 04 170 5104 000	Blatt/ page /
Mod.	Dat.	Name	D-32339 ESPELKAMP					
							Sub.	

Alle Rechte vorbehalten/ All rights reserved