




APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/12/20	



RECOMMENDED PCB LAYOUT



**SPECIFICATIONS:**

**Material:**

Housing: PBT, rated UL94V-0, Color: Black

Contact: Brass, Tin plated

**Electrical:**

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megohms ohms min

Dielectric Voltage: 500 VAC @ sea level

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE MILLIMETERS  
 TOLERANCES: EXCEPT AS NOTED  
 MM ANGLE  
 X ± 0.30 X ± 1°  
 X.X ± 0.25 X.X ± 0.5°  
 X.XX ± 0.20  
 X.XXX ± 0.10

APPROVALS		DATE
DRAWN	LH	3/12/20
CHECKED	MY	3/12/20
APPROVED		

**ADAM  
 TECH**  
 INTERCONNECTS

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

TITLE BATTERY HOLDER, PCB THRU HOLE  
 FOR 2032

SIZE X	PART NO. BH-25F-1	REV. -
REF: S00136C	SCALE: NTS	SHEET 1 OF 1