

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	15[mm]
Max. Air Flow:	19.4[CFM]
Max. Air Flow:	0.55[m ³ per min]
Max. Static Pressure:	0.27[In H ₂ O]
Max. Static Pressure:	67.7[Pa]
Fan Speed:	5600[RPM]
Noise:	36.5[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	60[g]
IP Rating:	IP68/IP69K
Tach / Locked Rotor Output:	No
Status:	Active