


APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/2/13	
A		UPDATED DRAWING	1/18/19	HR/RT
B		UPDATED SPEC.	10/7/20	LH/EY









RECOMMENDED PCB LAYOUT

SPECIFICATIONS:
Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Screw: M2.5 Steel
Contact: Copper Alloy, Tin Plated
Electrical:
Voltage rated: 300 V
Current rated: 15 A
Withstanding voltage: 1,600 for 1 minute
Mechanical:
Wire range: 30~14 AWG
Torque : 0.4 Nm
Strip length: 6~7mm
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

Positions: 2 thru 24
A= .197 [5.00] x No. of Positions
B= .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	8/2/13
CHECKED	NP	8/2/13
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

TERMINAL BLOCK, .197 [5.00] PITCH

SIZE	PART NO.	REV.
X	EBVA-XX-C	B

REF: S00067C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.