



Product Locator

Product List

- COM Express
- Fanless Embedded Systems
- Power Supplies
- Cellular/Satellite M2M
- Single Board Computers
- FPGA
- Digital I/O
- Analog I/O
- Qseven Carrier Boards
- Solid State Drives
- Ethernet-to-serial
- Wireless Radio Modems
- CAN Controllers
- Synchronous Serial
- PCI/104
- PCI/104-Plus
- PCI/104-Express
- PCI-104
- CompactPCI
- PCI Express
- PCI
- ISA
- FeaturePak
- USB-to-serial
- Development Tools
- Cables & I/O Boxes
- Custom Boards
- Industrial Temp. Boards
- Conformal Coating
- Web Specials

Product Search Results

Displaying page 9 of 14

[Previous](#) [Next](#)

Part Number: BLG022-05
Product Name: BlueStorm/LP RS-422/485
Bus Type: Universal PCI
Interface: RS-422/485
Ports: 4 ports
Cables: [CBG007](#)
Max Baud: 1843200 bps
Features: This BlueStorm/LP is built for installation in a low profile chassis. It includes an extra standard height mounting bracket, surge suppression and male DB-25 cables. RoHS compliant.



[product homepage](#)

Part Number: BLG024-01
Product Name: BlueStorm/LP RS-422/485
Bus Type: Universal PCI
Interface: RS-422/485
Ports: 4 ports
Cables: [CBG003](#)
Max Baud: 1843200 bps
Features: This BlueStorm/LP is a low profile PCI board equipped with a standard height mounting bracket. It includes a male DB-9 cable assembly, surge suppression and additional low profile bracket. RoHS Compliant.



[product homepage](#)

Part Number: BLG024-05
Product Name: BlueStorm/LP RS-422/485
Bus Type: Universal PCI
Interface: RS-422/485
Ports: 4 ports
Cables: [CBG007](#)
Max Baud: 1843200 bps
Features: This BlueStorm/LP is a low profile card built for installation in a standard height chassis. It includes surge suppression, an extra low profile bracket and male DB-25 cables. RoHS compliant.



[product homepage](#)

Part Number: BLG026-01
Product Name: BlueStorm/LP RS-232/422/485
Bus Type: Universal PCI
Interface: RS-232/422/485
Ports: 4 ports
Cables: [CBG003](#)
Max Baud: 1843200 bps
Features: This BlueStorm/LP is a low profile PCI board equipped with a low profile mounting bracket. It provides 2 ports RS-232 and 2 ports RS-422/485. Includes additional standard height bracket and DB-9 cables. RoHS compliant.



[product homepage](#)

Part Number: BLG026-05
Product Name: BlueStorm/LP RS-232/422/485
Bus Type: Universal PCI
Interface: RS-232/422/485
Ports: 4 ports
Cables: [CBG007](#)
Max Baud: 1843200 bps
Features: This BlueStorm/LP is built for installation in a low profile chassis and provides two RS-232 ports and two RS-422/485 ports. It includes an extra standard height mounting bracket, surge suppression and male DB-25 cables. RoHS compliant.



[product homepage](#)

Product Search Results

Displaying page 9 of 14

[Previous](#) [Next](#)