

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



**BD-03AFMM-QR8D01**

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: UL2238, UL50e

You must login first for view the price

Quantity - 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type 

Search

X-Lok, Standard...  
AB-BD03FL-BDHL  
-20°C ~ +105°C

- 0 +

X-Lok, Standard...  
AB-BD03FL-BDHL  
-20°C ~ +105°C

- 0 +

X-Lok, Standard...  
AB-BD03FL-BDHL  
-20°C ~ +105°C

- 0 +

X-Lok, Standard...  
AB-BD03FL-BDHL  
-20°C ~ +105°C

- 0 +

X-Lok, Standard...  
AB-BD03FL-BDHL  
-20°C ~ +105°C

- 0 +

X-Lok, Standard...  
AB-BD03FR-BDH...  
-20°C ~ +80°C

- 0 +

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 5A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 03
Connector Gender Female	Backshell Right Angle
Mating Style Push Lock	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK