

May 7, 2005

[Products](#)
[Accessories](#)
[New Products](#)
[Where to Buy](#)
[Service / Repair](#)
[Dist. Access](#)
[Online Tools](#)
[Warranty Reg.](#)
[Download](#)
[Application Notes](#)
[International](#)
[Join Our Newsletter](#)

E-Mail Address:

First Name:

Last Name:

[Subscribe](#)
[Unsubscribe](#)

Test Lab Starter Kit

Model#TL-55

For the first time student or new lab technician, here is a complete starter accessory kit. It contains the most commonly used products for instrument hookup

- leads, probes, hooks and alligator clips for DMMs, 150 MHz x1/x10 switchable oscilloscope probe, BNC cable and BNC adapters
- everything you'll need to get started. They are of the same high quality as B+K Precision offers individually but in one fully stocked kit. Get going in your profession with B+K Precision instruments and the convenient Model TL-55,

[| Datasheet | Features |](#)

TIP KIT ACCESSORIES f/TL 2

Model#TL 3

Threaded accessories to fit TL-2A probes

- Black and Red pairs (except for alligator clip) Alligator clip, Red only Spring hook clips 4" Sharp extension tips to reach tight test points No. 10 Spade lugs

Power Supply Test Leads Set

Model#TLPS

New accessory kit combines safety and functionality. The highly flexible silicone jacked test leads feature a retractile sheathed banana plug to connect to the Power Supply and a fixed sheath banana plug to protect the user. A complete selection of accessories are included -

- large alligator clips, standard alligator clips, spade lug and banana plug adapters -
- to make your connects easier. For Power Supplies with remote sensing capability, a ready-made lead set also included.

Function Generator Test Leads Set

General purpose test probe set that includes BNC to BNC cables, BNC adapters and test clips.

|

885 & 886 Shorting Bar

Model#TL885D

|

4 WIRE TEST LEAD (MODELS 885 & 886)

Model#TL885B

|

THERMOCOUPLE PROBE F/2906/2945

Model#TP 29

|

4-Wire Kelvin Test Leads with clip (model 885 & 886)

Model#TL08C

|

AIR & GAS PROBE -50 TO 800C

Model#TP 2A

|

Maxi-Pro DMM Kit

Model#TL-50 Complete accessory kit for all your testing needs. Includes soft, flexible silicone lead wire easy movement and Tri-Fold Velcro Pouch for convenient storage. All components compliant to IEC61010-2-031 Silicone lead wire length 60" (1.5m) Tri-fold Velcro Pouch

| [Datasheet](#) | [Features](#) |

810-875 3inch Plug to Clip Test Leads (red/blk)

Model#TL 830

|

Tweezer Test Lead (Surface Mount)

Model#TL 8 Two conductor leads 400V rms, 1A

|

5 AMP HOOK-UP CABLE SET

Model#TL 5A 4mm Banana plug to alligator clip 5A rating Black and Red pair 40" (1.0m) length

|

UNIVERSAL TEST LEAD SET

Model#TL 4 Economical replacement test leads. TL-1 has safety shrouded banana plugs. TL-4 has un-shrouded banana plugs. 1500V 3A ratings PVC lead wire, 40" (1.0m) Black and Red Alligator clips

|

30 AMP HOOK-UP CABLE SET

Model#TL 30 #10 Spade Lug to Large Battery Clips 30A rating Black and Red pair 30" (0.75m) length

|

TWEEZER SMD PROBE (MODELS 885 & 886)

Model#TL885A

|

5-WAY TEST CLIP TO Shth RtP, SILICONE, BLK/RED

Model#TL 140 5-Way Communication Clip 60" (1.5m) Silicone Leads

|

GENERAL PURPOSE DMM KIT

Model#TL 130A

| [Features](#) |

Test Probe Set, Low Cost IEC1010 (PVC) w/Alligator

Model#TL 100A IEC61010 600V CATIII Rating UL Listed Highly flexible PVC lead wire, 40" (1.0m) Black and Red Alligator clips

|

SMD Probe Kit

Model#TL 10 Extended, slim-line probe body for easy reach. Use with small SMD components or general purpose test points. Includes soft, flexible silicone lead wires for easy movement

|

SHEATHED TEST LEAD SET

Model#TL 1 Economical replacement test leads. TL-1 has safety shrouded banana plugs

|

IMMERSION PROBE, STANDARD -50 TO 900C

Model#TP 1A

|

AC/DC CLAMP ACCESSORY FOR DMMs

Model#CP 3

- Converts any DMM to a current clamp
- Measures current without disconnecting circuit under test
- Measures to 400A DC/AC
- Outputs 1mV per Amp, operates on 2V range of any DMM

| [Specs](#) |

DELUXE TEST LEAD SET

Model#TL 2A

IEC61010 1000V CATIII Rating Silicone Lead Wire length 60" (1.5m) Black
Alligator Clip included Threaded tips fits TL-3 Accessory kit items

|

SURFACE PROBE, RT-ANGLE -50 TO 400C

Model#TPK-05

| [Datasheet](#) |

PIERCING PROBE -50 TO 600C

Model#TPK-04

| [Datasheet](#) |

SURFACE PROBE, STANDARD -50 TO 400C

Model#TPK-03

| [Datasheet](#) |

K-TYPE TRANSITION TEMPERATURE ADAPTER FOR 2890

Model#TP-A

| [Datasheet](#) |

TEMPERATURE ADAPTER

Model#TP 30B

This self-powered adapter turns your multimeter into a thermometer. Measurement range is -58°F through 1832°F (-50°C through 1000°C). Input impedance of the meter must be at least 12k, and the range must cover 0 to 1VDC (analog or digital). The TP-30B uses K-type thermocouple. The TP-29 general purpose temperature probe is included. °F / °C selectable Measures temperatu

HIGH TEMP K TYPE PROBE

Model#TP 3

|

FLEXIBLE LEAD SETS (models 510, 510A 520B & 520C)

Model#FP 6

Specialized test lead set for B+K Precision semiconductor testers. Three conductor lead with 4mm banana plugs to mini-IC test clips.

- 3 conductors
- Yellow, Green and Blue
- 30" (76cm) length

|

Note: If you can't find the part number you're searching for then it might be an obsolete model. Try to search for it under [Service/Repair](#) section.

[Home](#) | [About B+K](#) | [Contact Us](#) | [Press Releases](#) | [F.A.Q.](#) | [Sitemap](#)

B&K Precision Corporation
22820 Savi Ranch Parkway
Yorba Linda, CA 92887 U.S.A.
Phone: (714) 921-9095, Fax: (714) 921-6422

[Switching Power Supply, Function Generator, Arbitrary Waveform Generator](#)
[Anemometer, Hygrometer, Programmer, Multimeter, Analog Oscilloscope, Spectrum Analyzer](#)
[Lcr / Esr meter, Capacitance Meter, Volt Meter, Current Clamp Meter, Ph Meter, Humidity Meter](#)