

Search within category

GO

BUY NOW

DESIGN / INSTALL



UTPCH2BLY

Category 5e, UTP patch cord with Pan-Plug™ Modular Plugs on each end. Black, 2 ft.
UTPCH2BLY replaces UTPCH2BL

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Note	UTPCH2BLY replaces UTPCH2BL
Performance Level	Category 5e
Cable Type	U/UTP
Cable Color	Black
Length (ft.)	2.00
Length (m)	0.6
Flammability Rating	CM
Termination End 1	Modular Plug
Termination End 2	Modular Plug
Standards	ANSI/TIA-568-C.2, ISO 11801 Class EA, IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.
CE Compliant	Yes
Nominal Cable O.D. (In.)	0.22
Nominal Cable O.D. (mm)	5.5
Operating Temperature	14°F to 140°F (-10°C to 60°C)
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
UL5A Listed	No
AWG Size	24
BMEcat - Type of Connector	RJ45 8(8)
Boot Color	No Boot
Conductor Material	Copper
Installation Temperature	-40°F to 158°F (-40°C to 70°C)
Part Features	100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch
RoHS Compliancy Status	Compliant
Min. Order Qty.	1