

DATEC-POCKET-BOX

Compact handheld enclosures

The attractive pocket-sized DATEC-POCKET-BOX plastic enclosures offer a remarkable amount of technology in a minimum of space, as well as sturdy construction.

- thin profile for comfortable holding
- plain surfaces allow easier machining for the interfaces
- battery compartments for N, AA, AAA and 9 V cells
- standard versions with pre-fitted sealing gaskets provide greater protection against dust and water entry
- recessed operating area for protecting the membrane keypad or decorative foil/label
- three sizes in two colors
- ABS (UL 94 HB) or PMMA plexiglas infra-red light-permeable (UL 94 HB); for efficient infra-red signals the recessed front face is clear polished (sizes M/L)
- belt/pocket clip as accessory
- internal fastening pillars for PCBs



DATEC-POCKET-BOX

Applications and Examples

- Especially suitable for measuring and control technology
- Remote controls
- Pulse generator for ultra-sound and infra-red
- Sensors, optoelectronics
- Mobile data recording
- Wireless communications



IR remote control for harsh environments



Radio transmitter for machines



Telemetric ECG system for veterinary medicine

View Customizing Options

What do you still need for your own very personal product? We can supply enclosures and tuning knobs with all necessary modifications for fitting your electronic components.
Customizing options for Datec-Pocket-Box



Machining



Lacquering



Printing



Laser marking



Decor foils



Special material



RFI/EMI shielding



Installation / Assembly
of accessories

DATEC-POCKET-BOX

Select Versions



A9070107
DATEC-POCKET-BOX S
ABS (UL 94 HB)
off-white RAL 9002
3.35"x1.81"x0.63"
IP 41



A9070109
DATEC-POCKET-BOX S
ABS (UL 94 HB)
black RAL 9005
3.35"x1.81"x0.63"
IP 41



A9070117
DATEC-POCKET-BOX S
ABS (UL 94 HB)
off-white RAL 9002
3.35"x1.81"x0.63"
IP 54



A9070119
DATEC-POCKET-BOX S
ABS (UL 94 HB)
black RAL 9005
3.35"x1.81"x0.63"
IP 54



A9070209
DATEC-POCKET-BOX S
PMMA (IR) (UL 94 HB)
black RAL 9005
3.35"x1.81"x0.63"
IP 41



A9070219
DATEC-POCKET-BOX S
PMMA (IR) (UL 94 HB)
black RAL 9005
3.35"x1.81"x0.63"
IP 54



A9071107
DATEC-POCKET-BOX M
ABS (UL 94 HB)
off-white RAL 9002
4.13"x2.28"x0.73"
IP 41



A9071109
DATEC-POCKET-BOX M
ABS (UL 94 HB)
black RAL 9005
4.13"x2.28"x0.73"
IP 41



A9071117
DATEC-POCKET-BOX M
ABS (UL 94 HB)
off-white RAL 9002
4.13"x2.28"x0.73"
IP 54



A9071119
DATEC-POCKET-BOX M
ABS (UL 94 HB)
black RAL 9005
4.13"x2.28"x0.73"
IP 54



A9071209
DATEC-POCKET-BOX M
PMMA (IR) (UL 94 HB)
black RAL 9005
4.13"x2.28"x0.73"
IP 41



A9071219
DATEC-POCKET-BOX M
PMMA (IR) (UL 94 HB)
black RAL 9005
4.13"x2.28"x0.73"
IP 54



A9072107
DATEC-POCKET-BOX L
ABS (UL 94 HB)
off-white RAL 9002
4.72"x2.56"x0.87"
IP 41



A9072109
DATEC-POCKET-BOX L
ABS (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 41



A9072117
DATEC-POCKET-BOX L
ABS (UL 94 HB)
off-white RAL 9002
4.72"x2.56"x0.87"
IP 54



A9072119
DATEC-POCKET-BOX L
ABS (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 54

DATEC-POCKET-BOX



A9072127
DATEC-POCKET-BOX L
ABS (UL 94 HB)
off-white RAL 9002
4.72"x2.56"x0.87"
IP 41



A9072129
DATEC-POCKET-BOX L
ABS (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 41



A9072209
DATEC-POCKET-BOX L
PMMA (IR) (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 41




A9072219
DATEC-POCKET-BOX L
PMMA (IR) (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 54



A9072229
DATEC-POCKET-BOX L
PMMA (IR) (UL 94 HB)
black RAL 9005
4.72"x2.56"x0.87"
IP 41

Accessory "battery"



A9160003
Plug-in contact, 1 x 9 V



A9190002
Set of battery clips,
2xN/2xAA/2xAAA
Steel
tin-plated



A9190003
Set of battery clips,
2xN/2xAA/2xAAA
Steel
nickel-plated



A9250251
Battery spacer
PE foam
1.97"x0.98"x0.12"

DATEC-POCKET-BOX

Accessory "carrying"



A9100001
Ring eyelet
PA 6
volcano



A9172107
Belt/Pocket clip
ABS (UL 94 HB)
off-white RAL 9002
2.44"x1.18"



A9172109
Belt/Pocket clip
ABS (UL 94 HB)
black RAL 9005
2.44"x1.18"

Accessory "screws"



A0304031
Self-tapping screws 0.087" x
0.197" (PZ1)



A0305031
Self-tapping screws 0.098" x
0.236" (PZ1)

Subject to technical modification without notice. © by OKW Gehäusesysteme, Buchen/Germany.