



Part Number : [1202480510](#)
Product Description : Brad Safety MPIS Distribution Box, Top-Mount, 8 Ports / 8-Pole, LED, WSOR Cable, 5.0m Length
Series Number : 120248
Status : Active
Product Category : Passive Distribution Boxes
Engineering Number : BTR831P-FBW-05



Documents & Resources

Drawings
[1202480510_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120248
Description	Brad Safety MPIS Distribution Box, Top-Mount, 8 Ports / 8-Pole, LED, WSOR Cable, 5.0m Length
IP Rating	IP67
Product Name	Brad Safety,MPIS
UPC	889056632959

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	Safety
Voltage - Maximum	10-30V DC
Wiring Configuration	Safety Wiring

Physical

Bus I/O	N/A
Cable Connector Orientation	Straight
Cable Length	5.0m
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail

Keyway	A-Coded
LED Indicator	Safety
Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	382.456/g
Orientation	Top-Mount
Poles	8
Poles (wired)	8
Ports	8
Temperature Range - Operating	-25°C to +85°C
Wire/Cable Type	WSOR

This document was generated on Sep 23, 2025