

CT2662

Fine Tip Digital Multimeter Probe

Pair, black & red, extended slimline probe bodies

Description

Black and red pair of probe bodies featuring one of the highest safety ratings of IEC 61010-031: 1,000 V CAT IV. They also provide extended lengths with very sharp stainless steel tips, ideal for a long reach and contact oxide piercing. The probes are supplied with clear, removable IC caps covering the tips.

Bodies accept 4 mm sheath (safety) banana plug test leads.

Features:

- 1,000 V CAT IV ratings
- Contact tips: Stainless Steel
- Clear, removable IC caps
- Long reach design: 136 mm (5.4") length

Individual colors available as Model CT2264



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT IV
Current Max	16 A
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

