



Part Number : [1301430243](#)
Product Description : Watertite Extreme Cordset,
14 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length
7.62m (25.0'), NEMA L15-20, 3ø 250V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Number : 26W75A144



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset, 14 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L15-20, 3Ø 250V
IP Rating	IP67
NEMA Configuration	NEMA L15-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678863030

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 250V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	125.000/kg

Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on Sep 10, 2025