

WI-M-16-XX-@

(Extra Heavy-Duty 16 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-16-@ is 16 AWG, 266/0.08 stranded, bare copper wire with highly flexible 0.126" (3.2mm) diameter silicone jacket.
- Ratings:

Current	25 Amps @ 200°C
Voltage	600V
Dielectric Strength	2 KV/Min
Spark Test	6 KV
Bend Radius	3D
Rated Temperature	-40°C to 200°C
Temperature Rating	FT2
- Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red