
HellermannTyton

Technical data sheet

Article number:
633-02050 HV1205



Product Group	For punched or drilled metal sheets
Product Family	Edge protection grommets
Material	Polyvinylchloride, flame retardant (PVC-FR)
Colour	Black (BK)

Flammability	UL 94 V0
Operating Temperature	-30 °C to +60 °C
Package Content	1000 pcs.
Package Content packed in	pcs.
Shore Hardness A	55±5

RoHS

created on 22. May 2026, 4:19 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.