

RJI Cabel 8XAWG 26/7, strand., 50m-ring

[Spotted an error?](#) |  [Print page](#)

Back 



Image is for illustration purposes only.
Please refer to product description.


- [Features](#)

➤ [Material properties](#)

➤ [Version](#)
- [Connection data](#)

➤ [Dimensions and weight](#)

➤ [Norms and specifications](#)

Part number:	09 45 600 0542
Description:	RJI Cabel 8XAWG 26/7, strand., 50m-ring
Type sheet:	 PDF

Features

RoHS conformity:	Yes
Shielding:	Foil screen and additional plaited cable
Transmission characteristics:	Category 6 / Class E up to 250 MHz, according to ISO/IEC 11 801:2002 and EN 50 173-1
Limiting temperature, min.:	-20 °C
Limiting temperature, max.:	80 °C
Limiting temperature (flexible), min.:	-20 °C
Limiting temperature (flexible), max.:	80 °C
Cable structure:	4 x 2, Twisted Pair, shielded, PIMF

 Top

Connection data

Cable diameter, min.:	6,3 mm
Cable diameter, max.:	6,9 mm

 Top

Material properties

Colour, cable:	yellow
Material, cable:	PVC

 Top

Dimensions and weight

Net Weight:	2,554 g
-------------	---------

 Top

Version

Cable length:	50 m
Cable type, copper:	8 AWG 26/7 stranded

 Top


Norms and specifications

Approval UL:	Yes
--------------	-----

 Top

[Login to MyHARTING](#)
for pricing and stock check

Quantity:

Shopping cart 

Email inquiry 

Need assistance?



Customer service

Your HARTING customer
service representative:

866-278-0306
CustomerService-USA@HARTING.com

Catalogue

Cable Assemblies



 [Browse](#)
 [Download](#)

Catalogue

Coaxial and Metric Connectors



 [Browse](#)
 [Download](#)

Downloads

Title	Download
Type sheet	 PDF
Cable Assemblies	 PDF
Coaxial and Metric Connectors	 PDF

Recently viewed - [Delete](#)



RJI Cabel 8XAWG 26/7,
strand., 50m-ring

[Show product details](#)

Recently searched

No searches have been done yet.

