



Part Number : 1301040041
Product Description : Haztex Incandescent
Hazardous and Wet Location Hand Lamp,
100W
Series Number : 130104
Status : Active
Product Category : Lamps and Lights
Engineering Number : 61430



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130104
Description	Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Family	Specialty Lighting
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861430

Agency

CSA	LR39801
UL	E30252

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Hazardous, Wet Location
Guard Included	Yes
Guard Type	Cast Aluminum
Height	419.10mm (16.500")
Lamp Type	A21

Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Net Weight	2213.530/g
Outlet	None
Packaging Type	Carton

This document was generated on Sep 30, 2024