Product Line

- Single Pair Ethernet
- ZConnect
- Ceres
  - Accessory
  - Large Size
  - Macro Size
  - Middle Size
  - Mini Size
  - Others (GBD)
  - Others (MAB)
  - Others (PLD)
  - Standard Size
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub






ABB-03PMFS-LC7001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: UL1977

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



Ceres, Standard Size,...
1BB-03AFMM-LL6A01
-20°C ~ +80°C



Ceres, Standard Size,...
1BB-03AFMM-LL6A02
-20°C ~ +80°C



Ceres, Standard Size,...
1BB-03AFMM-LL6A03
-20°C ~ +80°C



Ceres, Standard Size,...
1BB-03AFMM-LL6A04
-20°C ~ +80°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **10A**	Connector Type **Receptacle**
Shielded **Plastic, Non-shielded**	No. of Contacts **03**
Connector Gender **Male**	Backshell **Circular**
Mating Style **2 Points Lock**	IP Rating **IPX7**
Assembly Style **Solder**	

More Options

People Also Bought





ABB-03PMFS-...

AB-AZ17FL-AZF...

MSAP04FL-...



1CD-14BMMM-...

SS-030300-MF...

Downloaded from Arrow.com.