




NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.




PRESSURE SENSITIVE TAPE 0.040(1.0)
THICK WITH PROTECTIVE LINER. MOUNT
IS DESIGNED TO SUPPORT 0.30 lbs(136 g)
MAX. WEIGHT ON A CLEAN, DRY, SMOOTH,
GREASE-FREE SURFACE.

PANDUIT PART NO. *	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT lbs (g) / 100 pcs
ABMM-AT	MINIATURE INTERMEDIATE	0.113 (51.3)

- 1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL.
- 2) REMOVE PROTECTIVE LINER.
- 3) PLACE IN DESIRED LOCATION.
- 4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS.

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR EASY REMOVAL OF LINER.
- 3) MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).



ACTUAL SIZE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)			
CAD FILENAME/LAYERS		G00239ER_DC_ABMM_AT_08	
 PANDUIT CORP. TINLEY PARK, ILLINOIS			
ABMM-AT ADHESIVE BACKED MOUNT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± ---- (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± ----		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY AJV	MAT'L: ABS (ACRYLONITRILE BUTADIENE STYRENE)	SCALE NONE	DWG A SIZE
DATE 12-23-96		DRAWING NO. G00239ER	
CHK'D			