



C2G
Discontinued - 10ft (3m) Cat5e Non-Booted Unshielded (UTP) Network Crossover Patch Cable - Gray
Part No. 24512



This Cat5e network crossover patch cable is an ideal solution for connecting two computer to share files or data. The crossed pin configuration allows two computers to be connected peer-to-peer without the need for a hub or switch. This cable may also be used to connect network switches and hubs without an uplink port to other switches and hubs. This cable is constructed to meet all Cat5e TIA/EIA standards, and has been designed to drastically reduce both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality cable and a shortened body plug, this design minimizes Near-End Crosstalk (NEXT) levels.

Features & Benefits

- Perfect for networking two PCs together
- Standard RJ45 connectors
- Available in 7 colors to color-code a network
- Available in lengths up to 25ft

Specifications

General Info

Product Line	C2G	Replaced by Part Number	27823
Color	Gray	UPC Number	757120245124
Country Of Origin	Vietnam	Application Sector	Commercial, Industrial, Residential
Type	Cable		

Dimensions

Cable Length	10 ft	Outside Diameter	5.3 mm
--------------	-------	------------------	--------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat5e
Wiring Scheme	T568B	Wire Gauge	24 AWG
Shielded/Unshielded Cable	Unshielded	Conductor	4-Pair Twisted
Shield Type	UTP	Cable Type	Crossover, Ethernet Patch Cable
Jacket Rating	Standard / Non-Rated	Cable Diameter	5.3 mm
Connector Type	Non-booted	Indoor/Outdoor	Indoor
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male

Bandwidth	350 mHz	Operating Temperature	-20°-80°C
Insulation Material	HDPE (High-density Polyethylene)	Storage Temperature	-20° - 80° C