




SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S34A.6X0
15	39.14	33.32	25.18	24.54	19.18	D15S34A.6X0
25	33.03	47.04	39.12	38.25	33.12	D25S34A.6X0
37	69.32	63.50	55.68	54.71	49.68	D37S34A.6X0


```
Protection: 4 --> flash AU
            6 --> 0.76μ AU
```

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S34A.GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S34A.GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S34A.GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S34A.GX00LF

Protection: 4 --> flash AU
6 --> 0.76 μ AU

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	MASSON	2000/07/26	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	2000/07/26			0.XX	±0.1				
Chr	LEGARE	2000/07/26			0.XXX	±0.1				
Appr	LEGARE	2000/07/26	Product family		D-SUB		Spec ref -			
			title FEMALE CONNECTOR FOR FOOT STRAIGHT SOLDER TYPE FOR			dwg no C01-8646-0717			Rev. E	
catalog no			-			CUSTOMER			sheet	of 1

rev	ecn no	dr	date
B	-	ATC	2000/12/2
C	LS05-001	MPE	2005/03/1
D	LS05-0056	MPE	2005/06/3
E	LS06-0097	LGO	2006/07/2
-	-	-	-
-	-	-	-
-	-	-	-