



Part Number : [734205190](#)

Product Description : SMP-MAX Plug, Straight, Smooth Bore, Panel Mount, Threaded, 5.00mm Length, Tri-Metal Plating, One Piece Per Bag, 50 Ohms

Series Number : 73420

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734205190 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73420
Description	SMP-MAX Plug, Straight, Smooth Bore, Panel Mount, Threaded, 5.00mm Length, Tri-Metal Plating, One Piece Per Bag, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	SMP-MAX
Style	Panel
Type	Subminiature
UPC	887191124438

Electrical

Frequency	10 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 330 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Plug
Keying to Mating Part	N/A
Net Weight	8.705/g
Orientation	Straight

Packaging Type	Individual Bag
Panel Mount	Yes
Panel Mount Method	Thread-In
PCB Mounting	Round Post
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 18, 2025