Specifications



Photo is representative





Eaton TB300-12ST

Eaton Bussmann TB300 series panel mount terminal block connector, Breakdown voltage 7500V, 600V, 30A, Barrier, Twelve-pole, Black, Molded thermoplastic base, tin-plated brass terminal, stainless steel philslot screw

General specifications

PRODUCT NAME	Eaton Bussmann series TB300 panel mount terminal block
CATALOG NUMBER	TB300-12ST
UPC	051712358248
PRODUCT LENGTH/DEPTH	7.75 in
PRODUCT HEIGHT	0.81 in
PRODUCT WIDTH	1.33 in
PRODUCT WEIGHT	0.16 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer
PRODUCT TYPE	Panel mount terminal block

Powering Business Worldwide

Downloaded from Arrow.com.

Electrical ratings

AMPERAGE RATING	30A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Twelve-pole
TYPE	Barrier

Resources

CATALOGS	TB300-12ST~TB300 Series 12-Pole Barrier Strip Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2617
MULTIMEDIA	Bussmann series Fuseology

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.