




## Rack Rail Reducer Panel *PBAS Series*

**Note:** This product line has been discontinued as a stocked series on October 31, 2025.

 Information is for reference only. It has been replaced with **PA Series**.  
For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.

### Features



- Constructed in 14-gauge steel.
- EIA-compliant round punched hole or tapped 12-24 for 19" mounting.
- Converts standard 23-inch or 24-inch rack mounting rails to 19-inch rack mounting.
- Sold in pairs.
- Finished in textured RAL9005 black or RAL7035 light gray powder paint coat.
  - Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



### Accessories

- Hardware for Rack Mounting Solutions

### 23 to 19 Inch Rack Rail Reducer Panel

Part No.	Mounting Dimensions	
	Rack Units	Height
12-24 Tapped Black Finish		
PA2319001BK1	1U	1.75
PA2319003BK1	2U	3.50
PA2319005BK1	3U	5.25
PA2319007BK1	4U	7.00
PA2319008BK1	5U	8.75

### 24 to 19 Inch Rack Rail Reducer Panel

RAL9005 Semi-Gloss		Mounting Dimensions	
Black	RAL7035 Light Gray	Rack Units	Height
Part No.	Part No.		
PBAS19001BK2	PBAS19001LG2	1U	1.75
PBAS19003BK2	PBAS19003LG2	2U	3.50
PBAS19005BK2	PBAS19005LG2	3U	5.25
PBAS19007BK2	PBAS19007LG2	4U	7.00
PBAS19008BK2	PBAS19008LG2	5U	8.75
PBAS19010BK2	PBAS19010LG2	6U	10.50
PBAS19012BK2	PBAS19012LG2	7U	12.25
PBAS19014BK2	PBAS19014LG2	8U	14.00

Uses Clip-Nuts.



