HellermannTyton

Technical data sheet

Article number:
167-00201 CTHC-T555

Material	Polypropylene (PP)
Colour	Black (BK)

Diameter (D)	12.7 mm
Flammability	UL 94 HB
Halogen-free	Yes
Inside Ø (ID)	12.7 mm
Operating Temperature	-20 °C to +90 °C
Package Content	425 pcs.
Package Content packed in	pack

HF RoHS

created on 15. May 2026, 6:13 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.