

Representative Image

Catalog No. GSC500

Description: 2-PC OUTER SLV CONN GRN I.D. 0.50

UPC No 786210814063

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .500 Inches/12.70mm, Outer Diameter .550 Inches/13.97mm, Color Green, Soft Bronze, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Outer sleeve for the Hexagonal Range (the outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

Specifications

Material	Soft Bronze
Color	Green

Classifications

Brand Name	Sta-Kon
Sub Brand	Shield-Kon

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002650 Connection for screened wires
Model	2-part
Sleeve form	Outer sleeve
Insulated	N
Outer diameter sleeve	13.97 mm
Inner diameter sleeve	12.7 mm
Sleeve length	6.4 mm
Sleeve length	0.25 inch

Downloaded from Arrow.com.

ETIM	EC002650 Connection for screened wires
Colour code	Green
Compression shape	Round
Reel packaging	N

Downloaded from Arrow.com.