

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

7SE9-T

7SE9-T

REPLACES

RELEASE NO. PR-15152

M

DRAWING
NUMBER

3

ISSUE

CHECK


REVISIONS

A PRI 15152

JAS 24 OCT 86

B CO61515

CJH 21 APR 87




NOTE

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON $.375 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMENDED
- 3 - BASIC SWITCH HAS 24K SOLID GOLD CONTACT MATERIAL
- 4 YELLOW MARKING IS ON BOTH SIDES OF HOUSING TO IDENTIFY THAT THIS UNIT HAS GOLD CONTACTS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE----- 4 - 8 OZ
RELEASE FORCE----- 2 OZ MIN
PRETRAVEL----- .004 MIN
DIFFERENTIAL TRAVEL----- .004 MAX
OVERTRAVEL----- .003 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

10 VDC-----0.5 AMP
30 VOLTS DC RATING
INDUCTIVE---SEA LEVEL-----1/2 AMP
50,000 FT-----1/2 AMP
RESISTIVE---SEA LEVEL-----1 AMP
50,000 FT-----1 AMP
MAXIMUM INRUSH-----2 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$

ANGLES $\pm$
RAW MATERIAL - COMMERCIAL STANDARD

DIMENSIONS ARE IN INCHES AND ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

MICRO SWITCH STANDARDS APPLY

WEIGHT .26 OZ MAX

52848-B

DRAWN

CHECK KAG 24 OCT 86

CHECK KAG 24 OCT 86

A S 24 OCT 86