

Power Matters.™

Home > 1N711A (#5066)

Products

- Product Directory
- Applications Directory
- Parametric Search

1N711A (#5066)

Overview

Diagrams

Shipping TR14

| Electrical Rating                         | Symbol       | Min | Typ | Max  | Unit     |
|-------------------------------------------|--------------|-----|-----|------|----------|
| Dynamic Impedance                         | $Z_{\kappa}$ |     |     | 5.30 | $\Omega$ |
| Regulator voltage, reference voltage (dc) | $V_Z$        |     |     | 7.50 | V        |

| Maximum Electrical Rating | Symbol | Min | Typ | Max  | Unit |
|---------------------------|--------|-----|-----|------|------|
| Power Dissipation, Total  | $P_T$  |     |     | 0.25 | W    |
| Tolerance                 | Tol    |     |     | 5.00 | %    |

This part can be found in the following product categories:

Discretes > Diodes > Zener > Zener Voltage Regulator Diode

Related Links

- Technical support
- Sales Contacts
- Available Stock
- Sales Contacts
- RFQ/Samples