

97

HZ30

Tools and harnessing machines



Tongs for termination of Micromodul™ connectors in insulation displacement technology (IDT)

97

HZ30

Range of application

Connector	MICA
Pole number	4-16
Pitch	1,27 mm
State of delivery of connectors	lose
Processable conductor	flat cable 1.27 mm


Features

Application	laboratory and sample production, harness repair
Stroke capacity	ca. 240/h
Scope of functions and delivery	- Harnessing of bus cables possible - In transport case - The handle color may vary during a period of transition.

Dimensions and supply data

Dimensions (H x W x D)	50 mm x 60 mm x 240 mm
Weight	ca. 0,8 kg

Associated products

Harnessing equipment
 MICA

97

HZ30

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
HZ30	-	1	1