

- 
- Products
- Industry Solutions
- CAREERS
- Resources

- Find Distributor
- Contact Molex



7.92 W.A. W/LOCK Pink



Series image - Reference only

Status: New Business Not Supported

Replacement: Contact Molex

Series: [53521](#)

Category: Molex Parts

EU ELV:Not Relevant

EU RoHS:Compliant

EU RoHS Phthalates:Not Contained

China RoHS: 

REACH SVHC:Not Contained Per -ED/01/2017 (12 January 2017)

Low-Halogen Status:Not Low-Halogen

General

Status	New Business Not Supported
--------	----------------------------

Category Molex Parts

Series [53521](#)

UPC 800753469174

Physical

Net Weight 573.601/mg

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

[Check our list of old tooling that used to be available for this part](#)

Products

- Antennas
- Application Tooling
- Cable Assemblies
- Connected Lighting
- Connectors
- Copper Flex
- Electrical Products
- Industrial Automation
- Membrane Switches

Quick Links

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)

Resources

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trade
- Mobile Site
- Supplier Po

Stay Connected



Molex.com would like to place cookies on your computer to help us make this website better.

- [Optical Solutions](#)
- [Printed Electronic Solutions](#)

- [Sitemap](#)

- [Privacy Policy](#)
- [Tradeshows](#)

Help us make this website better.

To find out more about the cookies, see our [Privacy Policy](#). To accept cookies from this site, please click the 'I Accept' button.

I Accept

I Decline

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered to their respective owners.

© Copyright 2017