


技术规格承认书 (Specifications for Approval)

序号	名 称		规 格	备注	序号	名 称		规 格
1	型号(Model)		M125B02620WM12		11	畸变(Distortion)		-77% at ϕ 7.2mm
2	感测器(Sensor)		CCD/CMOS		12	MTF	Center	250 linepairs/mm
3	像面尺寸(Image Format)		1/2.5"				0.5Field	250 linepairs/mm
4	焦距(Focal Length)		2.6				0.7Field	250 linepairs/mm
5	通光孔径(Aperture, F/#)		2.0				1 Field	230 linepairs/mm
6	视场角 Field of view (H:V=4:3)	D6mm	(H)100.8°×(V)75°×(D)129°		13	照度(Relative Illumination)		70.5% at ϕ 7.2mm
7		D6.72mm	(H)113.6°×(V)84.5°×(D)147.2°		14	最近物距(M.O.D.)		0.1m
8		D7.2mm	(H)123.2°×(V)90°×(D)160°		15	镜头组成 (Lens Construction)		7-6+Filter
9	后焦距(Back Focal Length)		6.03mm		16	接口(Mount)		M12×0.5-6g
10	有效通光口径 (Effective Aperture)		ϕ 13mm	Front	17	外形尺寸(dimension)		ϕ 17×18.8mm
			ϕ 5.6mm	Rear	18	重量(Weight)		



					摄像头 Camera Lens					M125B02620WM12	
标记	处数	更改文件号		签字日期		图样标记 重 量 比 例			厦门力鼎光电技术有限公司 Xiamen Leading Optics Co., Ltd.		
设计			工 艺								
制图			标 准								
校对			批 准								
审核			日 期								
						共 1 张		第 1 张			