

Inpac, 19" chassis



- Grounding/earthing kit optional
- RAL 7030 powder coat finish, other colors available
- For assembly with 19" components or individually with mounting plates
- Three rows ventilation slots in base for air inlet
- Aluminum construction with die-cast front and rear frames
- IP 20, in accordance with IEC 60529
- External dimensions in accordance with IEC 60297-3-101
- Grounding/earthing connectors to: DIN EN 50178/VDE 0160, DIN EN 60950/VDE 0805, DIN EN 61010-1/VDE 0411 part 1, DIN EN 61010-1A2/VDE 0411 part 1/A1
- Modifications such as cutouts or dimensions available

Note:

- Max. installation space when fitting 19" components is 75 HP
- Scope of delivery includes screws to fix rear and front panels
- Cover- and base plate available in other colors



Catalog Number	Height U	Depth D mm	Width HP	h mm	h1	h2
10828-171	2	254.5	84	86.0	57.5	76.2
10828-172	2	314.5	84	86.0	57.5	76.2
10828-173	2	374.5	84	86.0	57.5	76.2
10828-151	3	254.5	84	130.5	102.0	57.15
10828-152	3	314.5	84	130.5	102.0	57.15
10828-153	3	374.5	84	130.5	102.0	57.15
10828-154	3	434.5	84	130.5	102.0	57.15
10828-156	4	254.5	84	174.5	146.5	101.6
10828-157	4	314.5	84	174.5	146.5	101.6
10828-158	4	374.5	84	174.5	146.5	101.6
10828-159	4	434.5	84	174.5	146.5	101.6
10828-168	6	374.5	84	263.5	235.4	190.5
10828-169	6	434.5	84	263.5	235.4	190.5

Select product specifications before modifying or adding to project list or requesting a quote.

Height U

Select ▾

Depth mm

Select ▾

[Clear Selection](#)

Documents



Main Catalog - Inpac

Recently Viewed



Inpac, 19" chassis

Connect With Us

