

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P004-008



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 8 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to eight feet. The 8-ft. (2.43 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 8-ft. (2.43 m) to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, servers and monitors to a PDU up to 8-ft. (2.43 m) away in your data center
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-008 C14 Male to C13 Female Power Cable, 8-ft. (2.43 m), Black

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332180476 |
| Product Type | PDU Extension Power Cord |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region | Global |
| INPUT | |
| Maximum Input Amps | 10 |
| Voltage Compatibility (VAC) | 250 |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C14 |
| Side B - Connector 1 | IEC-320-C13 |
| Connector Style | Straight |



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|------------------------------------|-----------------------------|
| Color | Black |
| Plug Color | Black |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 7.8mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 18 |
| Wire Gauge (OD - mm ²) | 0.82 |
| Power Cord Color | Black |
| Cable Length (ft.) | 8 |
| Cable Length (m) | 2.44 |
| Shipping Dimensions (hwd / in.) | 10.98 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 27.89 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.57 |
| Shipping Weight (kg) | 0.26 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 10% to 65% RH |
| Storage Humidity Range | 10% to 65% RH |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| Locking Power Cord | No |
| Locking | No |
| STANDARDS & COMPLIANCE | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|-------------------------------------|
| Product Certifications | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.