Specification Sheet

Part Number: MB3A10M4

Product Image

For use with HellermannTyton T18 - T30 cable ties to provide stability when securing bundles.
4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 0.6 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.

Rubber Adhesive Cable Tie Mount, 0.75" x 0.75", Use With T18-T30 Cable Tie, PA66, White, 1000/pkg

Article Number	151-28721
Type	MB3A
Color	White (WH)
Quantity Per	bag
Product Description	MB3A adhesive mounts are for use with HellermannTyton T18 - T30 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.

Downloaded from Arrow.com.

Short Description	Rubber Adhesive Cable Tie Mount, 0.75" x 0.75", Use With T18-T30 Cable Tie, PA66, White, 1000/pkg
Global Part Name	MB3A-PA66-WH
Length L (Imperial)	0.75
Length L (Metric)	19.0
Fixation Method	Screw Mounting and Adhesive
Width W (Imperial)	0.75
Width W (Metric)	19.0
Cable Ties	T18 - T30
Height H (Imperial)	.18
Height H (Metric)	4.6
Cable Tie Width Max (Imperial)	0.14
Cable Tie Width Max (Metric)	3.6
Mounting Hole Diameter D (Imperial)	0.12
Mounting Hole Diameter D (Metric)	3.0 mm
Mounting Hole Diameter D Max (Metric)	3.0

Downloaded from Arrow.com.

Mounting Hole Centers (Imperial)	0.52
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.