

## Han B Hood Side Entry HC 2 Reels M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 0547
Specification	Han B Hood Side Entry HC 2 Reels M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19300240547">https://b2b.harting.com/19300240547</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood
Type	High construction

### Version

Size	24 B
Version	Side entry
Cable entry	1x M32
Locking type	Single locking lever
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------



Pushing Performance  
Since 1945

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	220 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140126947
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors