



PRODUCT INFORMATION

Item	Content
Class Code	XJA042
Series	HT
Product number	RHT1C331MDN1
Category Temperature Range	-55 to +105 cel
Rated voltage	16 V
Rated capacitance	330 μ F
Tolerance rated capacitance	-20 to +20%
Tangent of loss angle	0.12
Leakage current (short term)	1056 μ A
Diameter : D	10 mm
Length : L	14 mm
Rated Ripple Current (at 100kHz)	4750 m A
ESR	16 m Ohm
Mass	1.32 g
Packing Type	Bulk(Long Lead)
Quantity in the standard packing	1600
Surface mounting flag	FALSE
Environmental Matter	Lead(Pb) free and RoHS compliant.
Product Lifecycle Stage	PROD
Type	Lead Type
Package Type	04 type(JIS C 5101-1)
Applications	Conductive Polymer Aluminum Solid Electrolytic Capacitors Radial Lead Type,High Temperature(125degC)
Applicable Specification	JIS C 5101-1,5101-4

[JAPANESE](#)

Copyright (C) 2007 NICHICON CORPORATION