



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
 1. BRASS PER QQ-B-626
 2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 3. PHOSPHOR BRONZE PER QQ-B-750
 4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 5. TEFLON MIL-P-19468

| | | | | | DIMENSIONS ARE IN MILLIMETERS | | | | PART NO. N6551A1-NT3G-50 | | Amphenol | |
|-----|--------------------|----------|---------|------|---------------------------------------|---------|--------|-------|--------------------------|-----------|----------------------|--|
| | | | | | UNLESS OTHERWISE SPECIFIED TOLERANCES | | | | APPROVED | DATE | | |
| 4 | CONTACT PIN | NOTE 3 | NOTE 4 | 1 | N6551A1-4-B | 0.5-6 | = ±0.2 | | | 10-11-01' | N PANEL RECEPT. JACK | |
| 3 | INSULATOR | NOTE 5 | NATURAL | 1 | N6551A1-3T-50-B | 6-30 | = ±0.4 | | | 10-11-01' | | |
| 2 | HOUSING WITH PANEL | NOTE 1 | NOTE 2 | 1 | N6551A1-2S | 30-120 | = ±0.6 | | | 10-11-01' | DRAWING NO. | |
| 1 | BODY | NOTE 1 | NOTE 2 | 1 | N7900-4 | 120-315 | = ±1 | | | 10-11-01' | KJ-N6551A1-NT3G-50 | |
| NO. | DESCRIPTION | MATERIAL | FINISH | Q'TY | DRAWING NO. | SCALE | 3/1 | ISSUE | A | FILE NO. | ITEM NO. | |