

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009921400

Status:

Obsolete

Overview:

kk

Description:

3.96mm (.156") Pitch KK® Crimp Terminal Housing, 14 Circuits

Documents:

Drawing (PDF)

Agency Certification

UL

E29179

General

Product Family

Crimp Housings

Series

3069

Application

Power

Overview

kk

Product Name

KK®

Physical

Circuits (maximum)

14

Color - Resin

Natural

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

No

Material - Resin

Nylon

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm (.156")

Temperature Range - Operating

0°C to +75°C

Material Info

Old Part Number

3069-142

Reference - Drawing Numbers

Product Specification

PS-99020-0087

Sales Drawing

SD-3069-N***



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3069Series

Mates With

2220 , 3190 , 3192 , 3243, 3246, A4042, 41661 , 41662 , 41671 , 41672 , 41681 , 41682 , 41701 , 41711 , 41721 , 41741 , 41761 , 41771 , 41772 , 41791 , 41792 , 42441 , 42461 , 42471 , 42491 , 42492

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION