




9	FERRULE	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex PART DESCRIPTION TNC BULKHEAD CRIMP JACK – 75 OHM (FOR RG-59/U CABLE)															
8	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1		DRAWN		M.ZHANG								06/17/10									
7	HUT HEX	BRASS	NICKEL	1		CHECKED																			
6	LOCK WASHER	BRASS	NICKEL	1		ISSUED						PART NO. 122163													
5	GASKET	RUBBER	RED	1		SHEET		1 OF 1																	
4	BARREL	BRASS	NICKEL	1		CAD FILE		C:/CONNEX/122163.DWG		DWG. NO.								122163.DWG		REV.		NC		SIZE	
3	INSULATOR	PTFE	NATURAL	1																					
2	BODY	BRASS	NICKEL	1																					
1	HOUSING	BRASS	NICKEL	1																					
DESCRIPTION		MATERIAL		FINISH		QTY																			