

Power It! Power Strip with 6 Right-Angle Outlets, 15 ft. (4.57 m) Cord, Transparent Switch Cover

MODEL NUMBER: TLM615NCRA



Highlights

- 6 right-angle outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Rugged metal case
- Keyhole mounting slots

Package Includes

- TLM615NCRA power strip
- Warranty information
- Instruction manual

Description

Tripp Lite's Power It! TLM615NCRA power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 6 right-angle NEMA 5-15R outlets, 15-ft. (4.57 m) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip with right-angle outlets

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 right-angle NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-ft. (4.57 m) AC power cord
- Rugged metal case provides extra safety and durability
- UL certification

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332135681
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row of 6 (right-angle)
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Color	Light Gray
Material of Construction	Metal
Antimicrobial	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between mounting tabs = 203.20mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	41.3mm
Receptacle Color	Light gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	39.37 x 6.10 x 16.51
Shipping Dimensions (hwd / in.)	15.50 x 2.40 x 6.50
Shipping Weight (kg)	1.36
Shipping Weight (lbs.)	3.00
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 2
Unit Dimensions (hwd / cm)	35 x 6.35 x 5.1
Unit Weight (lbs.)	2.8
Unit Weight (kg)	1.27
Mounting Details	Includes flanges
STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>