

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1804160104](#)
Status: **Active**
Overview: [LED Array Holders for Citizen and Similar COB Arrays](#)
Description: LED Array Holder for 28.00 by 28.00mm COB, Gold (Au) Plating, Nylon, One-Piece Design, without Tab Cap, Natural

Documents:
[3D Model](#) [Application Specification AS-180412-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-180419-007-001 \(PDF\)](#)
[Product Specification PS-180414-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E345583
General	
Product Family	Solid State Lighting
Series	180416
Array Type	Citizen
Beam Angle	N/A
Overview	LED Array Holders for Citizen and Similar COB Arrays
Product Name	Wire Trap Holder
Type	LED COB Array Holder
UPC	887191130972
Physical	
Base Type	N/A
Color Rendering Index (CRI)	N/A
Correlated Color Temp (CCT)	N/A
Depth	0.60mm
Flammability	94V-0
Lamp Type	N/A
Material - Metal	Copper Alloy
Mounting Style	Screws
Net Weight	3.180/g
Packaging Type	Tray
Electrical	
Lamp Wattage - Maximum	N/A
Lumens	N/A
Voltage (Fixture) - Maximum	300V DC
Wiring Style	Poke In Wire Traps
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-180412-001-001
Packaging Specification	PK-180419-007-001
Product Specification	PS-180414-001-001
Sales Drawing	SD-180416-104



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/71/2019 (16 July 2019) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[180416 Series](#)

Use With
28.00mm by 28.00mm COB

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION